



Model: 3023XXXX1

3' Logic+ Class II, Type A2 Biological Safety Cabinet
8" or 10" Sash Opening

Certified Product

- * NSF/ANSI 49 Listed
- * ETL Listed to UL 61010-1
- * CE Mark (230V Models)
- * CAN/CSA 22.2 No. 61010-1
- * ADA Compliant Operation

Exterior Superstructure

- * Double Wall Construction * Powder Coated Cold Rolled Steel
* Color: Glacier White
Interior Superstructure
* Type 304 Stainless Steel * Unitized Construction
* Removable, Seamless, Dished Work Surface with lift out knobs

Side Panels

- * Each Side * Removable * Color: Glacier White

Air Foil

- * Curved, Type 304 Stainless Steel Grill
- * Integral Armrest
- * Reserve—Air Secondary Airflow Slots

Sash

- * Vertical Travel
- * Tempered Safety Glass
- * 10 degree angle

Electrical

- * Energy efficient DC ECM blower operation
- * Direct drive LED lighting
- * Outlet:
 - * 115V Models:
 - * Duplex, 115V / 50/60 Hz / GFCI, one on each side
 - * 5 amp max
 - * 230V Models:
 - * Single-Plex, 230V / 50/60 Hz, one on each side
 - * 3 amp max
 - * With Dampened Self-Closing Flush Splash Cover
 - * ADA-compliant

MyLogic LCD Information Center

- * Interior mounted, color, touchpad control
- * Step-by-step instruction guides when programming
- * "Filter Life Remaining" bar graph for HEPA filter
- * Visual and audible alarms
- * Manual activation of duplexes, blower, light, etc.
- * Data output via mini USB

Airflow

- * Nominal inflow velocity of 105 feet per minute
- * Nominal downflow velocity of 55 feet per minute
- * Approximately 70% air recirculation

Filters

- * Supply & exhaust 99.99% efficient HEPA filters @ 0.3 μm
- * ISO Class 5 conditions per ISO 14644-1 & 2

Optional Packages:

- * Accessory Package:
 - * UV Light
 - * Vacu-Pass Cord & Cable Port Kit
 - * Service fixture – Right Side – 1/4 turn control handle
- * Telescoping Base Stand (non-welded)
 - * Work surface height of 30–37"
- * Ventus Canopy Connection

SCALE: SCALED TO FIT

Biological Safety Cabinets for:



LABCONCO CORPORATION • KANSAS CITY MO USA 64132
800-821-5525 / 816-333-8811 • labconco.com

No.	Date
_____	_____
_____	_____
_____	_____
_____	_____
_____	_____
_____	_____
Date:	
Drawing # 3023XXXX1	
Drawn By:	
Checked By:	
Approved By:	
Sheet No.	